



## Cart-Mounted Solvent Recycler

**Description:** Recycles xylene, xylene substitutes, alcohol and acetone with 90-95% recovery.

**Model Number:** **5 Gallon (20 Liter) Recycler**  
SLV-99-U-20 (120 V configuration)  
SLV-99-CE-20 (220/240 V configuration)  
**10 Gallon (40 Liter) Recycler**  
SLV-99-U-40 (120 V configuration)  
SLV-99-CE-40 (220/240 V configuration)

**Dimensions:** **5 Gallon (20 Liter) and 10 Gallon (40 Liter) Recyclers**  
24.25 inches wide, 67 inches high, 30.5 inches deep  
(62 cm wide, 170 cm high, 77 cm deep)  
Plus shelf/shroud on side: 4 inches (10 cm)

**Electrical Configurations:** 120 VAC, 15.0 A, 50/60 Hz  
220 VAC, 7.5 A, 50/60 Hz  
240 VAC, 8.2 A, 50/60 Hz

**Cycle Times:** Xylene: 60 to 75 minutes per gallon  
(15 to 20 minutes per liter)  
Ethanol: 90 to 115 minutes per gallon  
(20 to 30 minutes per liter)

**Specifications:**

- Fractional Distillation
- Microprocessor controlled, fully automated
- Automatic waste disposal
- No cool-down between runs
- Built-in spill containment
- Satisfies the latest Uniform Fire Code requirements for solvent distillation units
- No water hook-up or special ventilation required
- No hot surfaces – cool to the touch
- Mobile
- Electric fill pump
- [ETL Listed to UL 61010 and UL 2208](#) and comparable Canadian standards (CSA) for 120 V configuration
- Built to CE Standards

**Alternate Configuration: 2.5 Gallon Cart-Mounted Solvent Recycler**  
(available in North America only)

Model Number: SLV-99-U-10 (120 V configuration)



*5 Gallon Solvent Recycler*



*10 Gallon Solvent Recycler*